

Home > Product > Fingerprint Photography > MOVEED Forensic Multi-wavelength LEDs Light Source(ALS) Barrel Fingerprint Photograph System

Product

- Forensic Touch DNA
- Forensic Lab Equipment
- Forensic Laser System
- Multi-band Lights
- Fingerprint Photography
- Fingerprint Photography**
- Footwear Impression Light
- Crime Scene Lights
- Police Illumination
- Light Tower
- Applications
- Tools for crime scene investigation

MOVEED Forensic Multi-wavelength LEDs Light Source(ALS) Barrel Fingerprint Photograph System



Contact US

MP: 86-159-5714-4852
 Tel: 86-571-86987719
 Fax: 86-571-86431401
 E-mail: hzh1@lightmobile.com

Product details



I. INTRODUCTION

The observation instrument uses imported high brightness LED light source, aviation aluminum alloy housing and high-performance lithium-ion batteries. It is mainly used to observe and take photos of dust fingerprints and fluorescence powder fingerprints. Convenient charging, no memory effect.

Forensic ALS Barrel System designed with coaxial lights and oblique lights, containing built-in excitation light sources, allowing camera lens barrel mounted on BARREL SYSTEM, which prevents the ambient background lighting to interfere, and assists photography tasks on latent fingerprints photograph and maintain the photos quality. Capture photos as what you see in sight.

II. SPECIFICATION

Model: OR-GDZ10, battery voltage: 3.7V
Working time: >120 min, charging current: 500mA
Magnification times: 5 times, battery capacity: 1,000mAh

III. FEATURES

- 1, Ideal for observation, photography and evidence extraction.
- 2, Reveal evidence with excitation lights AND latent fingerprints shooting at the same time, stably & quality & easy.
- 3, Place target fingerprints in a darkroom.
- 4, Coaxial Lights: white 6500K, red 632nm, blue 452nm, UV 392nm; Oblique Lights: white 5600K, blue 460nm, green 510nm
- 5, Filters available: yellow, orange, red.

Recruitment agent, interested in contact email: hzh1@lightmobile.com

[Effect chart](#)

Related products



Dual Camera Multi-



Portable



Ultra-wide Multi-



MOVEED Forensic



Infrared 850nm Light

Copyright: Hangzhou Hengli Electronic Technology Co., Ltd. 2015-2025 ALL RIGHTS RESERVED.

Tel: 86-571-86431402 86-571-86987719 Fax: 86-571-86431401 E-mail: hzh1@lightmobile.com

Add: 3rd floor#301, No. 4 building, Dinglan Rd 118th, Jianggan District, Hangzhou City, Zhejiang Province, China